

Qualification Results Summary AD5755-1 LFCSP

QUALIFICATION PLAN / STATUS			
TEST	SPECIFICATION	SAMPLE SIZE	RESULTS
High Temperature Operating Life (HTOL)*	JEDEC <i>JESD22-A108</i>	9 x 45	Pass
Highly Accelerated Stress Test (HAST)*	JEDEC <i>JESD22-A110</i>	9 x 45	Pass
Temperature Cycle (TC)*	JEDEC <i>JESD22-A104</i>	9 x 45	Pass
Temperature/Humidity/Bias (THB)*	JEDEC <i>JESD22-A101</i>	3 x 77	Pass
High Temperature Storage Life (HTSL)	JEDEC <i>JESD22-A103</i>	3 x 77	Pass
Solder Heat Resistance (SHR)*	JEDEC/IPC <i>J-STD-020</i>	9 x 11	Pass
Latch-Up	JEDEC <i>JESD78</i>	±100mA	Pass
Electrostatic Discharge <i>Human Body Model</i>	ESDA/JEDEC <i>JS-001</i>	3/voltage	Pass ±1.8kV
Electrostatic Discharge <i>Machine Model</i>	JESD22-A115	3/voltage	Pass ±100V
Electrostatic Discharge <i>Field-Induced Charged Device Model</i>	JEDEC <i>JESD22-C101</i>	3/voltage	Pass ±1.0kV

*Preconditioned per JEDEC/IPC J-STD-020