

Table 4: ADG5208F ESD Test Results

ESD Model	Package	ESD Test Spec	RC Network	Highest Pass Level	First Fail Level	Class
FICDM	16-TSSOP_4.4	JS-002	1 Ω , Cpkg	$\pm 500\text{V}$	$\pm 750\text{V}$	C2a
HBM	16-TSSOP_4.4	JESD22-A114	1.5k Ω , 100pF	$\pm 2000\text{V}$	$\pm 2500\text{V}$	2