

H201

C202

C201

U201

H202

12...55V

+VM : GND

D402

R401 +5V → +Vcc\_I0

R402 +3,3V → +Vcc\_I0

U401

C401

C402

C403

R303

C302

U301

C304

R304

Q301

Q302

R305

C303

C310

C318

C307

R311

R306

C312

C313

C315

IC301

C305

C306

C314

C311

R203

R313

R310

Q303

Q304

U

C204

C203

V

W

U203

J201

1

2

R301

C404

U402

Fault

D401

R403

H204

TMC6100-Eval v1.2

TRINAMIC  
MOTION CONTROL

H203