



TOP VIEW




SIDE VIEW

TOLERANCES OF FORM AND POSITION	
aaa	0.150
bbb	0.100
ccc	0.100
ddd	0.050
eee	0.080



DIMENSIONS			
DIM	MIN.	NOM.	MAX.
A	0.700	0.750	0.800
A1	---	---	0.050
A2	---	0.530	0.580
A3	0.203 REF.		
b	0.150	0.200	0.250
b1	0.200	0.250	0.300
b2	0.250	0.300	0.350
b3	0.350	0.400	0.450
b4	0.400	0.450	0.500
D	4.25 bsc		
E	4.25 bsc		
L	0.450	0.550	0.650
L1	0.550	0.650	0.750
L2	1.150	1.250	1.350
L3	2.250	2.350	2.450
e	0.400 bsc		
e1	0.500 bsc		
e2	0.525 bsc		
e3	0.600 bsc		
e4	0.625 bsc		
e5	0.800 bsc		
k1	0.250 bsc		
k2	0.350 bsc		
k3	1.050 bsc		
k4	0.225 bsc		
k5	0.500 bsc		
k6	1.075 bsc		



BOTTOM VIEW

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5-2009.
3. COPLANARITY APPLIES TO THE TERMINALS AND ALL OTHER BOTTOM SURFACE METALLIZATION.
4. MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
7. Package code is F224A4FY+1.

-DRAWING NOT TO SCALE-



TITLE:
PACKAGE OUTLINE, 22L, FC2QFN PKG.,
4.25X4.25X0.75mm

APPROVAL
YUANYUAN WEN

DOCUMENT CONTROL NO.
21-100399

REV. B 1/1