






SYMBOL	COMMON DIMENSIONS		
	MIN.	NOR.	MAX.
A	0.775	0.875	0.975
A1		0.29	REF
A2		0.37	REF
A3		0.2	REF
D	4.4	4.5	4.6
E	4	4.1	4.2
W	0.15	0.2	0.25
L	0.25	0.3	0.35
e		0.4	BSC
e1		0.4	BSC
n		38	
D1		2.4	BSC
E1		2.4	BSC
SD		0.4	BSC
SE		0.2	BSC
aaa		---	
bbb		---	
ddd		0.08	

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5-2009
3. N IS THE TOTAL NUMBER OF TERMINALS.
4. PIN #1 ID ON TOP WILL BE LASER MARKED.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.
7. PACKAGE CODES: F384A4-1

-DRAWING NOT TO SCALE-



TITLE:
PACKAGE OUTLINE, 38L OLGA,
4.1x4.5x0.875mm

APPROVAL
YUANYUAN WEN

DOCUMENT CONTROL NO.
21-100323

REV. A 1/1