




TOP VIEW




SIDE VIEW



BOTTOM VIEW



J-J' Cross section



PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
W61A1+1	1.53	1.63	1.12	1.22	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeters.
4. Marking shown is for package orientation reference only.
5. Tolerance is $\pm 0.02\text{mm}$ unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.

—DRAWING NOT TO SCALE—

MAXIM			
TITLE: PACKAGE OUTLINE 6L WLP PKG. 0.5mm PITCH (PN04)			
APPROVAL TIE WANG 05-16-08	DOCUMENT CONTROL NO. 21-0224	REV. A	1/1