







COMMON DIMENSIONS	
A	0.64 ±0.05
A1	0.24 ±0.03
A2	0.40 REF
A3	0.04 BASIC
b	∅0.31 ±0.03
D1	0.50 BASIC
E1	1.00 BASIC
e	0.50 BASIC
SD	0.25 BASIC
SE	0.00 BASIC

PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
W61C1+1	1.52	1.62	1.00	1.10	NONE
W61C1+2	1.52	1.62	1.00	1.10	B2
W61E1+1	1.41	1.51	0.92	1.02	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -



TITLE
PACKAGE OUTLINE 6 BUMPS
WLP PKG. 0.5 mm PITCH,

APPROVAL

DOCUMENT CONTROL NO.

21-0463

REV.

D

1/1