





TOP VIEW




COMMON DIMENSIONS	
A	0.64±0.05
A1	0.19±0.03
A2	0.45 REF
A3	0.04 BASIC
b	ø0.27±0.03
D1	2.80 BASIC
E1	3.20 BASIC
e	0.40 BASIC
SD	0.20 BASIC
SE	0.00 BASIC

PKG. CODE	E	D	DEPOPULATED BUMPS
W723A3+1	3.88 ±0.06	3.37 ±0.06	NONE
W723B3+1	3.867 ±0.025	3.608 ±0.025	NONE
W723C3+1	3.817 ±0.025	3.487 ±0.025	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeters.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02mm unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front-side finish can be either Black or Clear.



BOTTOM VIEW

—DRAWING NOT TO SCALE—

TITLE: PACKAGE OUTLINE 72 BUMPS, WLP PKG. 0.4mm PITCH			
APPROVAL	DOCUMENT CONTROL NO.	REV.	1/1
	21-0477	D	