






TOP VIEW



SIDE VIEW

COMMON DIMENSIONS		
A	0.64	±0.05
A1	0.19	±0.03
A2	0.45	REF
A3	0.04	BASIC
b	∅0.27	±0.03
D1	1.20	BASIC
E1	1.60	BASIC
e	0.40	BASIC
SD	0.20	BASIC
SE	0.00	BASIC



BOTTOM VIEW

PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
W201A2+1	2.33	2.36	1.92	1.95	NONE
W201B2+1	2.16	2.19	1.60	1.63	NONE
W201D2+1	2.08	2.11	1.71	1.74	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

-DRAWING NOT TO SCALE-



TITLE PACKAGE OUTLINE
20 BUMPS, WLP PKG. 0.4mm PITCH

APPROVAL
TIE WANG
09/02/14

DOCUMENT CONTROL NO.
21-0544

REV. C 1/1