

Yellow denotes an increase in specification

Current Data Sheet IDD Limits

ADUM3200, 5.0V/5.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.3	1.7	mA
I _{DD2} - 1Mbps		1.0	1.6	mA
I _{DD1} - 10Mbps		3.5	4.6	mA
I _{DD2} - 10Mbps		1.7	2.8	mA
I _{DD1} - 25Mbps		7.7	10.0	mA
I _{DD2} - 25Mbps		3.1	3.9	mA

ADUM3200, 3.0V/3.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.8	1.3	mA
I _{DD2} - 1Mbps		0.7	1.0	mA
I _{DD1} - 10Mbps		2.0	3.2	mA
I _{DD2} - 10Mbps		1.1	1.7	mA
I _{DD1} - 25Mbps		4.3	6.4	mA
I _{DD2} - 25Mbps		1.8	2.4	mA

ADUM3200, 5.0V/3.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.3	1.7	mA
I _{DD2} - 1Mbps		0.7	1.0	mA
I _{DD1} - 10Mbps		3.5	4.6	mA
I _{DD2} - 10Mbps		1.1	1.7	mA
I _{DD1} - 25Mbps		7.7	10.0	mA
I _{DD2} - 25Mbps		1.8	2.4	mA

ADUM3200, 3.0V/5.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.8	1.3	mA
I _{DD2} - 1Mbps		1.0	1.6	mA
I _{DD1} - 10Mbps		2.0	3.2	mA
I _{DD2} - 10Mbps		1.7	2.8	mA
I _{DD1} - 25Mbps		4.3	6.4	mA
I _{DD2} - 25Mbps		3.1	3.9	mA

Revised Data Sheet IDD Limits

ADUM3200, 5.0V/5.0V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.3	1.8	mA
I _{DD2} - 1Mbps		1.0	1.6	mA
I _{DD1} - 10Mbps		3.5	4.6	mA
I _{DD2} - 10Mbps		2.0	2.8	mA
I _{DD1} - 25Mbps		7.7	10.0	mA
I _{DD2} - 25Mbps		3.8	4.9	mA

ADUM3200, 3.3V/3.3V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.8	1.3	mA
I _{DD2} - 1Mbps		0.7	1.0	mA
I _{DD1} - 10Mbps		2.2	3.2	mA
I _{DD2} - 10Mbps		1.3	1.7	mA
I _{DD1} - 25Mbps		4.8	6.4	mA
I _{DD2} - 25Mbps		2.3	3.0	mA

ADUM3200, 5.0V/3.3V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.3	1.8	mA
I _{DD2} - 1Mbps		0.7	1.0	mA
I _{DD1} - 10Mbps		3.5	4.6	mA
I _{DD2} - 10Mbps		1.3	1.7	mA
I _{DD1} - 25Mbps		7.7	10.0	mA
I _{DD2} - 25Mbps		2.3	3.0	mA

ADUM3200, 3.3V/5.0V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.8	1.3	mA
I _{DD2} - 1Mbps		1.0	1.6	mA
I _{DD1} - 10Mbps		2.2	3.2	mA
I _{DD2} - 10Mbps		2.0	2.8	mA
I _{DD1} - 25Mbps		4.8	6.4	mA
I _{DD2} - 25Mbps		3.8	4.9	mA