

Qualification Results Summary PML9315 Inductor

LTM8025				
Test	Specification	Conditions	Sample Size (lots x samples)	Results
High Temperature Operating Life (HTOL)	JEDEC JESD22-A108	1000h, T _j = 125C	1 x 77	Pass
ESD, HBM	JS-001	2000V	3 / Voltage	Pass
ESD, FICDM	ESDA/JEDEC JS-002	750V	3 / Voltage	Pass
Temperature Cycle (TC)*	JEDEC JESD22-A104	1000cyc, -55C/+125C	1 x 77	Pass
Thermal Shock (TS)	JEDEC JESD22-A106	1000cyc, -55C/+125C	1 x 77	Pass
Unbiased Highly Accelerated Stress Test (UHAST)*	JEDEC JESD22-A118	264h, 110C/85%RH	1 x 77	Pass
High Temperature Storage Life (HTSL)	JEDEC JESD22-A103	1000h, 150C	1 x 50	Pass

* Tests are preceded by MSL 3 Preconditioning: 48h 125C bake, 192h 30C/60% unbiased soak, and 3 reflow passes at 245C peak.

LTM8050				
Test	Specification	Conditions	Sample Size (lots x samples)	Results
Temperature Cycle (TC)*	JEDEC JESD22-A104	1000cyc, -55C/+125C	1 x 77	Pass
Thermal Shock (TS)	JEDEC JESD22-A106	1000cyc, -55C/+125C	1 x 77	Pass
Unbiased Highly Accelerated Stress Test (UHAST)*	JEDEC JESD22-A118	264h, 110C/85%RH	1 x 77	Pass
High Temperature Storage Life (HTSL)	JEDEC JESD22-A103	1000h, 150C	1 x 25	Pass

* Tests are preceded by MSL 3 Preconditioning: 48h 125C bake, 192h 30C/60% unbiased soak, and 3 reflow passes at 245C peak.