






DIMENSION	COMMON DIMENSIONS		
	MIN.	NOM.	MAX.
A3	0.195	0.203	0.211
b	0.20	0.25	0.30
D	1.925	2.000	2.075
E	1.925	2.000	2.075
e	0.65 BSC		
L	0.25	0.30	0.35
PKGCODES: D622N+1; D622N+2; D622N+3; D622N+4; D622N+5; D622N+6			

DIMENSION	DIMENSION VARIATIONS		
	MIN.	NOM.	MAX.
A	0.55	0.60	0.65
E2	1.25	1.35	1.45
D2	0.55	0.65	0.75



NOTES:

1. DIMENSION & TOLERANCING CONFORM TO ASME Y14.5M-1994.
2. ALL DIMENSIONS ARE IN MILLIMETERS.
3. DIMENSION b APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.20mm AND 0.30mm FROM TERMINAL TIP.
4. MARKING SHOWN IS FOR REFERENCE ONLY
5. ALL DIMENSIONS APPLY TO PbFREE (+) PKGCODES ONLY.

-DRAWING NOT TO SCALE-



TITLE:
PACKAGE OUTLINE, 6L, 2x2 OPTO TDFN PKG.
NiPd PLATING

APPROVAL	DOCUMENT CONTROL NO. 21-0490	REV. E	1/1
----------	---------------------------------	-----------	-----