


# POWER SOLUTIONS FOR PRECISION TECHNOLOGY SIGNAL CHAINS

## PRECISION CURRENT SENSING Generic Signal Chains for Current Measurement Shunt: Common-Mode Voltage Level Up to $\pm 600V$

Rev. 0 | Aug. 2022



©2022 Analog Devices, Inc. All rights reserved.  
Trademarks and registered trademarks are the  
property of their respective owners.

This document is interactive. You can click on any underlined text to navigate through the document.

For the resources:

APPENDIX	<u>Parts Guide</u>
	<u>Power Requirements</u>

Left-click the Parts Guide and Power Requirements to go through the list of power devices and other references.

The Power Components are listed on the Appendix, and you may click on the part to go through its product page online.

PART #	DESCRIPTION
<u>LT3471</u>	Dual 1.3A, 1.2MHz Boost/Inverter in 3mm × 3mm DFN
<u>LT8604</u>	High Efficiency 42V/120mA Synchronous Buck
<u>LT8570-1</u>	Boost/SEPIC/Inverting DC/DC Converter with 65V Switch, Soft-Start and Sync.

For the individual pages:

Left-click the specific signal chain to go through its respective block diagram or power tree.

Non-isolated	<b>POWER RE</b>
<u>1-Channel</u>	
	<b>PARAMETER</b>
	Supply Voltage
	Supply Current
	PSRR

Precision Current Sensing

APPENDIX

[Parts Guide](#)


[USER GUIDE](#)

[Power Requirements](#)

Generic Signal Chain for Current Measurement

Shunt: Common-Mode Voltage up to  $\pm 600V$

Isolated  
Multichannel



Precision Current Sensing

Generic Signal Chain for Current Measurement

Shunt: Common-Mode Voltage up to ±600V

Isolated

Multichannel

PART #	DESCRIPTION
<b><u>ADP7118</u></b>	20 V, 200 mA, Low Noise, CMOS LDO Linear Regulator
<b><u>LT3032-15</u></b>	Dual 150mA Positive/Negative Low Noise Low Dropout Linear Regulator
<b><u>LT3472</u></b>	Boost and Inverting DC/DC Converter for CCD Bias
<b><u>LT8604</u></b>	High Efficiency 42V/120mA Synchronous Bucks
<b><u>ADuM3471</u></b>	Isolated Switching Regulators (3/1 Channel Directionality)

Isolated

Multichannel

## POWER REQUIREMENTS

PARAMETER	STAGES	Difference Amp		Filter	ADC			Isolation	Reference
	Part #	AD8479		-	AD7172-4			ADuM3471	ADR4550
	Pin	+V <sub>S</sub>	-V <sub>S</sub>		AV <sub>DD1</sub>	AV <sub>DD2</sub>	IOV <sub>DD</sub>	V <sub>DD1</sub>	IN
Supply Voltage	V	15	-15	-	3.3	3.3	5	5	15
Supply Current	mA	0.85	-0.85	-	1.9	1.1	0.98	46	0.95
PSRR	dB	20 (500kHz)	0 (300kHz)	-	132 (1MHz)			-	60 (1MHz)

**Note 1:** The supply currents indicated are the maximum quiescent current of the supply rails. For overall full load or short circuit current specifications, refer to the datasheets of the signal chain components.

**Note 2:** The supply voltages indicated are the values for typical applications.

**Note 3:** Consult the corresponding datasheets for details on: (1) power supply rejection ratio (PSRR) and (2) power dissipation.

**Note 4:** The actual supply current requirement shall be multiplied depending on the number of channels on the signal chain.