





108-Terminal Land Grid Array [LGA]
(10mm × 20mm × 2.75mm)
(Reference DWG # CC-108-3)



DIMENSIONS				
SYMBOL	MIN	NOM	MAX	NOTES
A	2.65	2.75	2.85	
A1			0.03	
L	0.30	0.40	0.50	
b	0.22	0.25	0.28	
D		10.00		
E		20.00		
D1		4.00		
E1		17.75		
e		0.50		
H1		0.25 REF		SUBSTRATE THK
H2		2.50 REF		MOLD CAP HT
aaa			0.10	
bbb			0.10	
ccc			0.10	
ddd			0.10	
eee			0.15	
fff			0.08	

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
2. ALL DIMENSIONS ARE IN MILLIMETERS
3. PRIMARY DATUM -Z- IS SEATING PLANE
4. METAL FEATURES UNDER THE SOLDER MASK OPENING NOT SHOWN SO AS NOT TO OBSCURE THESE TERMINALS AND HEAT FEATURES
5. DETAILS OF PIN 1 IDENTIFIER ARE OPTIONAL, BUT MUST BE LOCATED WITHIN THE ZONE INDICATED. THE PIN 1 IDENTIFIER MAY BE EITHER A MOLD OR MARKED FEATURE
6. THE EXPOSED HEAT FEATURE IS SEGMENTED AND ARRANGED IN A MATRIX FORMAT. IT MAY HAVE OPTIONAL CORNER RADII ON EACH SEGMENT