





		SYMBOL	MIN	NOM	MAX
TOTAL THICKNESS		A	0.8	0.85	0.9
STAND OFF		A1	0	0.035	0.05
MOLD THICKNESS		A2	---	0.65	0.67
L/F THICKNESS		A3	0.203 REF		
LEAD WIDTH		b	0.2	0.25	0.3
BODY SIZE	X	D	5 BSC		
	Y	E	5 BSC		
LEAD PITCH		e	0.5 BSC		
PACKAGE EDGE TOLERANCE		aaa	0.1		
MOLD FLATNESS		bbb	0.1		
COPLANARITY		ccc	0.08		
LEAD OFFSET		ddd	0.1		
EXPOSED PAD OFFSET		eee	0.1		

DIMENSION VARIATION TABLE					
PKG CODE	DESCRIPTION	SYMBOL	MIN	NOM	MAX
K2855+1C	EP SIZE	J	3	3.1	3.2
		K	3	3.1	3.2
	LEAD LENGTH	L	0.5	0.55	0.6
K2855+2C	EP SIZE	J	3.6	3.7	3.8
		K	3.6	3.7	3.8
	LEAD LENGTH	L	0.35	0.40	0.45

NOTES

- ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
- COPLANARITY APPLIES TO LEADS, CORNER LEADS AND DIE ATTACH PAD.
- MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
- ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.



TITLE:
PACKAGE OUTLINE, 28L, SAWN QFN-CU
5X5X0.9mm

APPROVAL
KAI LIU

DOCUMENT CONTROL NO.
21-100584

REV. 1
B

-DRAWING NOT TO SCALE-