

PCN 12_0224

Qualification Results

| TEST NAME | SPECIFICATION | SAMPLE SIZE | RESULTS |
|--------------------------|---|-------------|---------|
| High Temp Operating Life | 500 Hrs @ +125 °C T-junction minimum | 16 | Pass |
| Temperature Cycle | JESD22, Method A104-A Condition J 0°C to +100°C. 1000 Cycles | 32 | Pass |
| Mechanical Shock | MIL-STD-202G Method 2002.4 2000g | 6 | Pass |