

Reliability Qualification Results of 3x3 sawn LFCSP package at ATP

QUALIFICATION RESULTS			
TEST	CONDITIONS	SAMPLE SIZE	RESULTS
Highly Accelerated Stress Test (HAST)*	JEDEC <i>JESD22-A110</i>	3 x 77	Pass
Temperature Cycle (TC)*	JEDEC <i>JESD22-A104</i>	3 x 77	Pass
Autoclave (AC)*	JEDEC <i>JESD22-A102</i>	3 x 77	Pass
Solder Heat Resistance (SHR)*	<i>JEDEC/IPC J-STD-020</i>	3 x 11	Pass

*These samples were subjected to preconditioning (per J-STD-020 Level 3) prior to the start of the stress test. Level 1 preconditioning consists of the following: Bake: 24 hrs @ 125°C, Soak: Unbiased Soak: 192 hrs @ 30°C, 60%RH, Reflow: 3 passes through an oven with a peak temperature of 260°C.