

Click here to ask an associate for production status of specific part numbers.

# **Evaluates: 1-Wire Peripheral and iButton Devices**

# DS9481R USB-to-1-Wire/ iButton Adapter

#### **General Description**

The DS9481R is a USB-to-1-Wire® adapter for easy PC connectivity to 1-Wire devices. The adapter provides an RJ11 connector with the signals to communicate with all 1-Wire and įButton® devices that support a 3.3V data I/O level. Additionally, the adapter provides the support and signaling to program 1-Wire/įButton EEPROM and one-time programmable (OTP)/EPROM devices. To provide a total hardware solution, the DS9481R can readily be used with the DS9120 socket adapter to create a 1-Wire PC programmer for 1-Wire peripheral devices (contact factory for more information). The equivalent peripheral hardware solution for the iButton is the DS1402D-DR8.

### **Adapter Contents**

QTY	DESCRIPTION
1	USB-to-1-Wire adapter Analog Devices DS9481R-3C7+
1	USB Type A-to-USB Mini-Type B cable Qualtek Electronics Corp. 3021003-03

#### **Features**

- Driver Support for Windows® 11 and Windows 10 Operating Systems
- Enumerates as a Virtual PC COM Port by Use of the Prolific PL-2303GC USB-to-UART Bridge IC
- Emulates the DS2480B 1-Wire Line Driving Functionality
- 1-Wire OTP/EPROM Programming Provided Without the Need of an External Power Supply (12V on OW, 7V on PULSE)
- 3.3V Read/Write Operation to 1-Wire/<u>i</u>Button Devices
- RJ11 Interface for Standard Connectivity Accessories such as the DS9120 Socket Adapter
- Supports Standard and Overdrive 1-Wire Communication
- Provides Strong Pullup to 3.3V
- Fully Compliant with USB 2.0 Specification

### **Ordering Information**

PART	TYPE
DS9481R-3C7+	Adapter

<sup>+</sup>Denotes lead(Pb)-free and RoHS compliant.

## DS9481R USB-to-1-Wire/iButton Adapter



1-Wire and <u>i</u>Button are registered trademarks of Maxim Integrated Products, Inc. Windows is a registered trademark of Microsoft Corporation.

19-5608; Rev 1; 3/23

# Evaluates: 1-Wire Peripheral and iButton Devices

#### **Quick Start**

#### **Recommended Equipment**

- Analog Devices DS9481R (included in adapter)
- USB type-A to USB Mini type-B cable (included in adapter)
- RJ11 cable assembly (not included)
- PC with a Windows 11 or Windows 10 OS and a spare USB port

**Note:** In the following sections, software-related items are identified by bolding. Text in **bold** refers to items directly from the adapter software. Text in **bold and underlined** refers to items from the Windows operating system.

#### **Procedure**

- 1) Do the following to install the PL-2303GC Prolific driver:
  - a) Download the latest driver version from Prolific.
  - b) **Open** and **Run** the latest version of the Driver Installer.
  - c) Follow the directions of the <u>Install Wizard</u> until <u>Finish</u> is reached for the PL-2303 USB-to-serial driver installation. Close by clicking the <u>Finish</u> button.

- 2) Do the following to install the 1-Wire drivers:
  - a) Go to the <u>Download 1-Wire/iButton Drivers for Windows</u> webpage..
  - b) From the **Choose Operating System** drop-down list, select your OS.
  - From the Select File drop-down list, select 32-bit or 64-bit 1-Wire drivers for the architecture being used by your OS.
  - d) Click the **Download** button.
  - e When prompted by the question **Do you want to run or save this file?**, select **Run**.
  - f) When you get a security warning that says **Do** you want to run the software?, select **Run**.
  - g) Read and check the box if you accept the license agreement and click **Install**.
  - h) Click the Finish button to exit the Setup Wizard.
- 3) The DS9481R USB-to-1-Wire adapter uses both the Prolific PL-2303GC and the Analog Devices MAXQ610 to emulate a virtual COM-to-1-Wire port on any PC. Find the enumeration of the virtual COM port by inserting the DS9481R into a spare USB port on the computer. Determine the COM port by looking in Control Panel→System→Hardware→Device Manager and expand Ports (COM & LPT). The port is COM5 in the example shown in Figure 2.



Figure 1. DS9481R USB-to-1-Wire/iButton Adapter and Cable

Evaluates: 1-Wire Peripheral and <u>i</u>Button Devices

You have now completed the installation of the DS9481R adapter. Obtain the adapter software and directions for installation for your 1-Wire/<u>i</u>Button peripheral device by contacting the Analog Devices online <u>Technical Support Portal</u>.

#### **Detailed Description of Connectors**




Figure 2. DS9481R COM Port




Figure 3. 1-Wire RJ11 Port

#### Table 1. 1-Wire RJ11 Pinout

CONNECTOR PIN	SIGNAL NAME
1	3.3V
2	GND
3	OW (DATA)
4	OWGND
5	PULSE
6	GP

#### **RJ11 Pinout**

Table 1 and Figure 3 show the RJ11 pinout mounted on the DS9481R PCB at J1. The RJ11 pin 1 can supply 3.3V and can be used for auxiliary board power. The GND is the ground of the 3.3V supply. The signal OW (DATA) stands for the 1-Wire data bus. The ground return for OW (DATA) is the signal OWGND. The PULSE signal is to be used as the VCC power supply for OTP 1-Wire peripheral parts. The PULSE signal is typically 3.3V, but also can provide the needed programming pulse for OTP parts. The GP signal is reserved for future general-purpose usage and is functionally not used by the DS9481R.

#### **Mini-USB Pinout**

The 5-position Mini-USB type AB connector is mounted at CN1 of the DS9481R PCB, as shown in Table 2.

#### Hardware/Firmware Capabilities

The DS9481R uses both the Prolific PL-2303GC and the Analog Devices MAXQ610. The PL-2303GC is fully compliant with the USB 2.0 specification for the Windows 11 and Windows 10 OS and provides a bridge for the USB-to-UART connection. The MAXQ610 is loaded with firmware that emulates the functionality of the DS2480B serial-to-1-Wire line driver at a lower 3.3V operation voltage. The MAXQ610 functions as a UART-to-1-Wire bridge and can serve custom application needs with firmware programmability.

Table 2. Mini-USB Type AB USB Pinout

CONNECTOR PIN	SIGNAL NAME
1	5.0V
2	DMCN
3	DPCN
4	NC
5	GND
6-9	GND_EARTH

Evaluates: 1-Wire Peripheral and <u>i</u>Button Devices

## **DS9481R EV Kit Bill of Materials**

DESIGNATION	QTY	DESCRIPTION
C1, C6, C21	3	4.7uF, 16V Y5V ceramic capacitors (0805)
C1, C0, C21	3	TDK Corp. C2012Y5V1C475Z
C2, C3	2	2.2uF, 16V Y5V ceramic capacitors (0805)
C2, C3		Murata GRM21BF51C225ZA01L
C4, C7	2	0.22uF Q10%, 16V X7R ceramic capacitors (0603)
C4, C7		TDK Corp. C1608X7R1C224K
CE C4E C22	3	10nF ±5%, 16V X7R ceramic capacitors (0603)
C5, C15, C22		AVX 06035C103JAT2A
00 040 040 044 000 000	6	0.1uF, 16V X7R ceramic capacitors (0603)
C8, C12, C13, C14, C20, C23		KEMET C0603C104K4RACTU
040	1	10uF, 10V Y5V ceramic capacitor (0805)
C10		TDK Corp. C2012Y5V1C106Z
0.10	0	Do not populate,
C16		470pF ceramic capacitor (0603)
0.7	2	1uF, 10V X7R ceramic capacitor (0603)
C17, C18		Taiyo Yuden LMK107B7105KA-T
C26	1	2.2uF, 16V X5R ceramic capacitors (0603)
		, the second sec
	1	10pF, 16V NP0 ceramic capacitor (0603)
C19		TDK Corp. C1608C0G1H100D
C9, C24, C25	0	Do not populate, capacitors
CN1	1	USB Mini-AB connector, right-angle, SMD, 5-position JAE Electronics DX3R005HN2E700
	1	30V, 200mA Schottky diode (SOT23)
D1	· ·	Diodes Inc./Zetex BAT54TA
	1	15V, 350mA zener diode (SOT23)
D2	,	Diodes Inc. MMBZ5245B-7-F
	1	Orange LED (TSS type) (0603)
D3		Panasonic/SSG LNJ812R83RA
	1	Dual CC Schottky diode (SOT23)
D4		
	2	Diodes Inc./Zetex BAT54CTA
FB1, FB2		220W, 2000mA ferrite chips (0805)
	4	Murata BLM21PG221SN1D
J1	1	6-position, right-angle, PCB-mounted jack
10		Tyco 5520425-3
J2	0	Do not populate, JTAG connector
Q1, Q3	2	130mA, 50V p-channel MOSFETs (SOT23-3)
		Fairchild Semiconductor BSS84
Q2, Q4, Q5, Q7	4	115mA, 60V n-channel MOSFETs (SOT23)
	4	Diodes, Inc. 2N7002-7-F
Q6	1	3.9A, 20V p-channel MOSFET (SOT23)
		NXP PMV65XP,215
R1, R29	0	Do not populate,
		resistors
R2, R3, R5	0	Do Not Populate Resistors
. ,		
R4, R16, R21	3	1.5kOHM Q1%, 1/10W SMD resistors (0603)
		Panasonic ECG ERJ-3EKF1501V
R6, R24	2	10kOHM Q1%, 1/10W SMD resistors (0603)
<u></u>		Yageo RC0603FR-0710KL
R7, R14, R26	3	1kOHM Q1%, 1/10W SMD resistors (0603)
, ,		Yageo RC0603FR-071KL
R8, R13, R17, R20, R27, R30	5	100kOHM Q1%, 1/10W SMD resistors (0603)
,, , , , , , , , , , , , , , , ,		Yageo RC0603FR-07100KL

Evaluates: 1-Wire Peripheral and <u>i</u>Button Devices

# **DS9481R EV Kit Bill of Materials (continued)**

DESIGNATION	QTY	DESCRIPTION
R9	1	979Ohm Q5%, 1/10W SMD resistor (0603)
K9		Yageo RC0603FR-07750RL
R10, R29	1	00hm Q1%, 1/10W SMD resistor (0603)
		Panasonic ECG ERJ-3GEY0R00V
R11	1	33Ohm Q1%, 0.1W SMD resistor (0603)
KII		Rohm MCR03EZPFX33R0
D12 D15 D22	3	4.99Ohm Q1%, 1/10W SMD resistors (0603)
R12, R15, R22		Yageo RC0603FR-074R99L
R18	1	2.2kOHM Q5%, 1/10W SMD resistor (0603)
KIO		Stackpole Electronics RMCF 1/16 2.2K 1% R
R19	1	4.7k OHM Q5% (0603)
R23	1	51kOHM Q0.1%, 1/10W SMD resistor (0603)
R23		Panasonic ECG ERA-3AEB513V
R25	1	11kOHM Q0.1%, 1/10W SMD resistor (0603)
R25		Vishay/Dale TNPW060311K0BEEA
R28	1	100hm Q1%, 1/10W SMD resistor (0603)
R26		Yageo RC0603FR-0710RL
D24	1	32.4kOHM Q1%, 1/10W SMD resistor (0603)
R31		Vishay/Dale TNPW060332K4BEEA
R32	1	30.1kOHM Q0.1%, 1/10W SMD resistor (0603)
R32		Panasonic ECG ERJ-3EKF3012V
D00	1	50kOHM Q1%, 1/10W SMD resistor (0603)
R33		Panasonic ECG ERJ-3EKF4992V
R36	1	27 Ohm Q1%, 1/10W SMD (0603)
RT1	1	0.12A, 30V PTC resettable fuse (1206)
KII		Bourns MF-NSMF012-2
SW1	0	Do not populate, switch
	1	Low-dropout, 300mA linear regulator (5 SOT23)
U1		Analog Devices MAX8887EZK33+T
		(Top Mark: ADPZ)
U2	1	12V, 30mA Flash memory programming supply (8 SO)
02		Analog Devices MAX662ACSA+
U3	1	TinyLogicM UHS inverter (5 SOT23)
03		Fairchild NC7SZ04M5X
U4	0	Do not populate, Silicon oscillator
U5	1	USB-to-serial bridge controller (28 SSOP)
03		Prolific PL-2303GC SSOP
U6	1	16-bit microcontroller with infrared module (32 TQFN-EP*)
		Analog Devices MAXQ610A-9410+
	1	2-channel ESD protector (6 FDFN)
U7		Analog Devices MAX13204EALT+
		(Top Mark: BV)
	1	High-voltage, low-power linear regulators (5 SOT23)
U8		Analog Devices MAX1616EUK+
		(Top Mark: ABZD)
U9	1	1.8V comparator (5 SOT23) STMicroelectronics TS3021ILT
_	1	PCB: DS9481R REV A5




Figure 4. DS9481R Adapter Board Schematic






Figure 5. DS9481R Adapter Enclosure Dimensions

Evaluates: 1-Wire Peripheral and <u>i</u>Button Devices


## **DS9481R EV Kit PCB Layout**






DS9481R Adapter Board—Top Assembly

DS9481R Adapter Board—Bottom Assembly




DS9481R Adapter Board—Top Silkscreen


## **DS9481R EV Kit PCB Layout (continued)**







DS9481R Adapter Board—Bottom Assembly



DS9481R Adapter Board—Top Silkscreen

Evaluates: 1-Wire Peripheral and iButton Devices

## **Revision History**

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	10/10	Initial release	_
1	3/23	Updated for hardware changes	All