

1/9/2013



**PRODUCT RELIABILITY REPORT
FOR**

MAX34460 Rev A2

Maxim Integrated

**14460 Maxim Dr.
Dallas, TX 75244**

Approved by:

**Don Lipps
Manager, Reliability Engineering**

Conclusion:

The following qualification successfully meets the quality and reliability standards required of all Maxim Integrated products:

MAX34460 Rev A2

In addition, Maxim Integrated's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maximintegrated.com/qa/reliability/monitor>.

Device Description:

A description of this device can be found in the product data sheet. You can find the product data sheet at <http://www.maximintegrated.com/search/parts.mvp>.

Reliability Derating:

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$$AfT = \exp((Ea/k) * (1/Tu - 1/Ts)) = tu/ts$$

AfT = Acceleration factor due to Temperature
tu = Time at use temperature (e.g. 55°C)
ts = Time at stress temperature (e.g. 125°C)
k = Boltzmann's Constant (8.617 x 10⁻⁵ eV/°K)
Tu = Temperature at Use (°K)
Ts = Temperature at Stress (°K)
Ea = Activation Energy (e.g. 0.7 ev)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7ev will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$$AfV = \exp(B * (Vs - Vu))$$

AfV = Acceleration factor due to Voltage
Vs = Stress Voltage (e.g. 7.0 volts)
Vu = Maximum Operating Voltage (e.g. 5.5 volts)
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$$Fr = X / (ts * AfV * AfT * N * 2)$$

X = Chi-Sq statistical upper limit
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$MTTF = 1/Fr$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

FAILURE RATE: **MTTF (YRS):** **108525** **FITS:** **1.1**
DEVICE HOURS: **871094719** **FAILS:** **0**

Only data from Operating Life or similar stresses are used for this calculation.

The parameters used to calculate this failure rate are as follows:

Cf: 60% **Ea: 0.7** **B: 0** **Tu: 25 °C** **Vu: 3.6 Volts**

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. **Bold** Product Number denotes specific product data.

Device Information:

Process: TSMC 0.18um Mixed signal, Embedded Flash, General Purpose, Two Poly Five Metal, 1.8V/3.3V Polyimide - No
Passivation: SiO/SiN
Die Size: 105 x 109
Number of Transistors: 730688
Interconnect: Aluminum / 0.5% Copper
Gate Oxide Thickness: 32 Å

ESD HBM

| DESCRIPTION | DATE | CODE/PRODUCT/LOT | CONDITION | READPOIN | QTY | FAILS | FA# |
|-----------------|------|------------------|---------------------------------------|----------|-------|----------|-----|
| ESD SENSITIVITY | 1219 | MAX34451 | ZJ133319BC JESD22-A114 HBM 500 VOLTS | 1 | PUL'S | 5 | 0 |
| ESD SENSITIVITY | 1219 | MAX34451 | ZJ133319BC JESD22-A114 HBM 1000 VOLTS | 1 | PUL'S | 5 | 0 |
| ESD SENSITIVITY | 1219 | MAX34451 | ZJ133319BC JESD22-A114 HBM 1500 VOLTS | 1 | PUL'S | 5 | 0 |
| ESD SENSITIVITY | 1219 | MAX34451 | ZJ133319BC JESD22-A114 HBM 2000 VOLTS | 1 | PUL'S | 5 | 0 |
| ESD SENSITIVITY | 1219 | MAX34451 | ZJ133319BC JESD22-A114 HBM 2500 VOLTS | 1 | PUL'S | 5 | 0 |
| Total: | | | | | | 0 | |

LATCH-UP

| DESCRIPTION | DATE | CODE/PRODUCT/LOT | CONDITION | READPOIN | QTY | FAILS | FA# |
|---------------|------|------------------|---------------------------------------|----------|-----|----------|-----|
| LATCH-UP I | 1219 | MAX34451 | ZJ133319BC JESD78A, I-TEST 25C 100mA | | | 6 | 0 |
| LATCH-UP I | 1219 | MAX34451 | ZJ133319BC JESD78A, I-TEST 25C 250mA | | | 6 | 0 |
| LATCH-UP V | 1219 | MAX34451 | ZJ133319BC JESD78A, V-SUPPLY TEST 25C | | | 6 | 0 |
| Total: | | | | | | 0 | |

OPERATING LIFE

| DESCRIPTION | DATE CODE | PRODUCT/LOT | CONDITION | READPOIN | QTY | FAILS | FA# |
|-------------------|-----------|-------------|--|----------|-----|-------|-----|
| HIGH TEMP OP LIFE | 0814 | MAXQ1103 | QN089294A 125C, 3.6V (PSA) & 2.0V (PSB) | 1000 HRS | 77 | 0 | |
| HIGH TEMP OP LIFE | 0828 | MAXQ2010 | QK086138C 125C, 3.6 VOLTS | 1000 HRS | 76 | 0 | |
| HIGH TEMP OP LIFE | 0837 | MAX2990 | QN096322A 125C, 3.6V (PSA) & 2.0V (PSB) | 1000 HRS | 77 | 0 | |
| HIGH TEMP OP LIFE | 0851 | MAXQ3108 | QJ091011AC 125C, 3.6 VOLTS | 192 HRS | 73 | 0 | |
| HIGH TEMP OP LIFE | 0851 | MAXQ610 | QJ091123AB 125C, 3.6V (PSA) & 2.0V (PSB) | 1000 HRS | 77 | 0 | |
| HIGH TEMP OP LIFE | 0852 | MAXQ1850 | QJ091074AA 125C, 3.6 VOLTS | 192 HRS | 75 | 0 | |
| HIGH TEMP OP LIFE | 0906 | MAXQ61H | QJ091049AB 125C, 3.6 VOLTS | 192 HRS | 45 | 0 | |
| HIGH TEMP OP LIFE | 0909 | MAXQ8913 | NQQ8ZAD 125C, 3.6V (PSA) & 5.0V (PSB) | 192 HRS | 77 | 0 | |
| HIGH TEMP OP LIFE | 0934 | MAXQ1103 | QN101437A 125C, 3.6V (PSA) & 2.0V (PSB) | 192 HRS | 77 | 0 | |
| HIGH TEMP OP LIFE | 0946 | MAXQ622 | QN091481C 125C, 3.6V (PSA) & 5.5V (PSB) | 192 HRS | 77 | 0 | |
| HIGH TEMP OP LIFE | 0951 | MAXQ61C | QJ101202AC 125C, 3.6 VOLTS | 192 HRS | 45 | 0 | |
| HIGH TEMP OP LIFE | 1006 | MAXQ1004 | QS101775AB 125C, 3.6V (PSA) & 5.0V (PSB) | 192 HRS | 45 | 0 | |
| HIGH TEMP OP LIFE | 1011 | MAXQ3103 | QJ101246AB 125C, 3.6 VOLTS | 192 HRS | 48 | 0 | |
| HIGH TEMP OP LIFE | 1011 | MAXQ3103 | QJ101246AB 125C, 3.6 VOLTS | 1000 HRS | 77 | 0 | |
| HIGH TEMP OP LIFE | 1024 | MAXQ1010 | QJ101790AG 125C, 5.5V (PS1) & 3.6V (PS2) | 192 HRS | 45 | 0 | |
| HIGH TEMP OP LIFE | 1024 | MAX31782 | QJ102013AC 125C, 5.5 VOLTS | 192 HRS | 45 | 0 | |
| HIGH TEMP OP LIFE | 1030 | MAXQ613 | QJ101861CH 135C, 3.6 V (PSA) | 192 HRS | 45 | 0 | |
| HIGH TEMP OP LIFE | 1050 | MAXQ6831 | ZN112250BC 125C, 3.6V (PSA), 1.89V (PSB) & 2.94V (PSD) | 1000 HRS | 48 | 0 | |
| HIGH TEMP OP LIFE | 1111 | MAXQ618 | ZJ112624AD 125C, 3.6 VOLTS | 192 HRS | 48 | 0 | |
| HIGH TEMP OP LIFE | 1119 | MAXQ1740 | ZJ112746BA 125C, 3.6 VOLTS | 192 HRS | 48 | 0 | |
| HIGH TEMP OP LIFE | 1120 | DS4830 | ZS112802AC 125C, 3.3 VOLTS | 192 HRS | 77 | 0 | |
| HIGH TEMP OP LIFE | 1134 | MAXQ1050 | ZS123062AB 125C, 5.5V (PSA) & 3.6V (PSB) | 192 HRS | 48 | 0 | |
| HIGH TEMP OP LIFE | 1135 | MAXQ610 | ZJ111435FC- 125C, 3.6V (PSA) & 2.0V (PSB) | 1000 HRS | 77 | 0 | |
| HIGH TEMP OP LIFE | 1135 | MAXQ610 | ZJ111435BD 125C, 3.6V (PSA) & 2.0V (PSB) | 1000 HRS | 77 | 0 | |
| HIGH TEMP OP LIFE | 1135 | MAXQ610 | ZJ111438BB- 125C, 3.6V (PSA) & 2.0V (PSB) | 1000 HRS | 77 | 0 | |

