

Bidirectional, On-The-Fly Programmable Gain, Current-Sense Amplifier with Wide Measurement Range

General Description

The MAX49918 is a high-precision current-sense amplifier (CSA) with an I^2C programmable gain option from 10V/V to 200V/V in 8 steps. The multiple programmable gain options offer maximum flexibility for the user to change gain on-the-fly.

The IC operating input common-mode range from -5V to +70V, with protections that extend down to -6V and up to +80V, thus providing protection against reverse-battery and high-voltage spikes.

The low input offset of $\pm 1\mu V$ (typ) and low gain error of $\pm 0.01\%$ (typ) make this device best-suited for high-precision current measurements.

The IC operates from a supply voltage of +2.7V to +5.5V with a typical quiescent supply at 0.7mA. The device operates over the full -40°C to +125°C temperature range.

The IC features bidirectional current sensing and is offered in a 3mm x 3mm, 10-pin TDFN package.

Applications

- Monitoring Distinct Current Levels
- Using the Same Current-Sense Resistors Across
 Multiple System Variants
- Requires a Non-Typical Gain Value Due to Sense Resistor Constraints
- H-Bridge Motor and Solenoid Current Sensing
- Battery Current Monitoring
- High- and Low-Side Precision Current Sensing

Benefits and Features

- Programmable Gain Options through I²C from 10V/V to 200V/V (8 steps)
- ±1µV (typ) Input Offset Voltage for REF1 = REF2 = V_{DD}/2
- ±5µV (typ) Input Offset Voltage for REF1 = V_{DD} and REF2 = GND at Gain = 20V/V
- ±0.01% (typ) Gain Error
- -5V to +70V Input Voltage Range
- -6V to +80V Protective Immunity
- 70kHz, -3dB Bandwidth at Gain = 20V/V
- 145dB DC CMRR
- Rail-to-Rail Output
- 3mm x 3mm, TDFN-10 Package
- -40°C to +125°C Temperature Range

Ordering Information appears at end of data sheet.

Simplified Block Diagram



Absolute Maximum Ratings

RS+ and RS- to GND	6V to +80V
RS+ to RS	±2V
V _{DD} to GND	0.3V to +6V
OUT, REF1, REF2 to GND	0.3V to V _{DD} + 0.3V

Continuous Current	into Pins			±	:10mA
Continuous Power	Dissipation	(Multi	Layer	Board)	(T _A =
+70°C, derate 24.4r	nW/°C above	+70°C)	1951	.2mW
Operating Temperat	ture Range		4	0°C to +	125°C
Storage Temperatur	e Range		6	5°C to +	150°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Package Information

10 TDFN

Package Code	T1033+1C
Outline Number	<u>21-0137</u>
Land Pattern Number	<u>90-0003</u>
Thermal Resistance, Four-Layer Board:	
Junction to Ambient (θ _{JA})	41°C/W
Junction to Case Thermal Resistance (θ_{JC})	9°C/W

For the latest package outline information and land patterns (footprints), go to <u>www.maximintegrated.com/packages</u>. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

Electrical Characteristics

 $(V_{CM} = V_{RS+} = V_{RS-} = +50V, V_{DD} = +3.3V, V_{SENSE} = V_{RS+} - V_{RS-} = 0V, V_{REF1} = V_{DD}/2, V_{REF2} = V_{DD}/2, G = 20V/V, T_A = -40^{\circ}C$ to +125°C, unless otherwise noted. Typical values are at T_A = +25°C (Note 1))

PARAMETER	SYMBOL	CONDITIONS		MIN	TYP	MAX	UNITS
POWER SUPPLY CHAR	ACTERISTICS						
Supply Voltage	V _{DD}	Guaranteed by PSR	R	2.7		5.5	V
Supply Current	I _{DD}	No loads			0.7	1	mA
Power-Up Time	^t PWR_UP	Output settles to 1%			200		μs
CURRENT-SENSE AMP	LIFIER						
DC CHARACTERISTICS	;						
Input Protected Common-Mode Range	V _{CM_P}			-6		+80	V
Input Common-Mode Range	V _{CM}	Guaranteed by CMF	Guaranteed by CMRR			+70	V
Input Bias Current (<u>Note 2</u>)	I _{RS+} , I _{RS-}				0.5	150	nA
Input Offset Current (<u>Note 2</u>)	I _{RS+} - I _{RS-}				0.1	50	nA
Input Leakage Current (<u>Note 2</u>)	I _{RS+} , I _{RS-}	V _{DD} = 0V, V _{RS±} = 70V			1	200	nA
			T _A = +25°C		±1	±10	
	oltage V _{OS}	For all gain options	-40°C ≤ T _A ≤ +125°C			±50	- μV
Input Offset Voltage		V _{REF1} = V _{DD} , V _{REF2} = GND	$T_A = +25^{\circ}C$		±5	±40	
			-40°C ≤ T _A ≤ +125°C			±80	
Input Offset Voltage Drift (<u>Note 2</u>)	TCV _{OS}				50	400	nV/°C
Power Supply Rejection Ratio	PSRR	$2.7V \le V_{DD} \le 5.5V;$ -	40°C ≤ T _A ≤ +125°C	95	125		dB
Common-Mode Rejection Ratio	CMRR	$-5V \leq V_{CM} \leq +70V; -$	40°C ≤ T _A ≤ +125°C	130	145		dB
Reference Voltage Rejection Ratio	RRRR	V _{REF} = 1.5V to 2.5V +125°C	; -40°C ≤ T _A ≤	90	115		dB
Input Capacitance	C _{IN}	RS+, RS- input			4.5		pF
Gain (<u>Note 3</u>)	G	I ² C Programmable			10 20 40 50 80 100 160 200		V/V
Gain Switching Time	t _{GAIN}	Settle within 1% of the	ne 1V final value		25		μs
	6-		T _A = +25°C		±0.01	±0.1	
Gain Error	GE	For all gain options	-40°C ≤ T _A ≤ +125°C			±0.2	%
Nonlinearity Error		$10mV \le V_{SENSE} \le 10mV$	100mV; G = 10V/V		0.01		%
Output Resistance	R _{OUT}	$V_{OUT} = V_{DD}/2$, I_{OUT}	- = ±500μA		0.3		Ω

PARAMETER	SYMBOL	CONDITIONS		MIN	ТҮР	MAX	UNITS
Output Voltage Swing High	V _{OH}	Source 500µA		V _{DD} - 0.015			V
Output Voltage Swing Low	V _{OL}	Sink 500µA				15	mV
Output Voltage Swing High	V _{OH}	No Load		V _{DD} - 0.004			V
Output Voltage Swing Low	V _{OL}	No Load	No Load			4	mV
Output Short-Circuit Current	I _{SC}	Shorted to either	^r V _{DD} or GND		55		mA
AC CHARACTERISTICS							
		G = 10V/V	$V_{SENSE} = 1V_{PP}/G$		75		
		G = 20V/V	V _{SENSE} = 1V _{PP} /G		70		
		G = 40V/V	V _{SENSE} = 1V _{PP} /G		60		
	DW	G = 50V/V	V _{SENSE} = 1V _{PP} /G		55		
Signal Bandwidth	BM ^{-3dB}	G = 80V/V	V _{SENSE} = 1V _{PP} /G		45		kHz
		G = 100V/V	V _{SENSE} = 1V _{PP} /G		40		
		G = 160V/V	V _{SENSE} = 1V _{PP} /G		30		
		G =200V/V	V _{SENSE} = 1V _{PP} /G		25		
Output Slew Rate	SR	2V _{PP} output squ V _{DD} /2	2V _{PP} output square wave, centered at Vחח/2		0.3		V/µs
AC Power Supply Rejection Ratio	AC PSRR	f = 200kHz, 100r	f = 200kHz, 100mV _{PP} sine wave		35		dB
AC Common-Mode Rejection Ratio	AC CMRR	f = 200kHz, 100r	f = 200kHz, 100mV _{PP} sine wave		60		dB
Capacitive Load	Cusur	With 250Ω isolat	ion resistor		20		nF
Stability	CLOAD	Without any isola	ation resistor		200		pF
Input Voltage Noise Density	e _n	At 1kHz			100		nV/Hz
Settling Time (Settling to 0.1%)	t _S	V _{SENSE} steps fr	om -50mV to 50mV		20		μs
I ² C INTERFACE TIMING	(400kHz I ² C)			-			-
SCL Clock Frequency	f _{SCL}					400	kHz
START Hold Time	^t HD:STA			600			ns
START Setup Time	t _{SU:STA}	90% of SCL to 9	0% of SDA	600			ns
Clock Low Period	t _{LOW}			1.3			μs
Clock High Period	t _{HIGH}			600			ns
Data Setup Time	t _{SU:DAT}	10% of SDA to 1	0% of SCL	100			ns
Data Hold Time	thd:dat	10% of SDA to 1	0% of SCL	0		900	ns
SCL Max Rise and Fall Time	t _R , t _F				300		ns
SDA Max Rise and Fall Time	t _R , t _F				300		ns
STOP Condition Setup	t _{SU:STO}	90% of SCL to 1	0% of SDA	600			ns

 $(V_{CM} = V_{RS+} = V_{RS-} = +50V, V_{DD} = +3.3V, V_{SENSE} = V_{RS+} - V_{RS-} = 0V, V_{REF1} = V_{DD}/2, V_{REF2} = V_{DD}/2, G = 20V/V, T_A = -40^{\circ}C$ to +125°C, unless otherwise noted. Typical values are at T_A = +25°C (Note 1))

Bidirectional, On-The-Fly Programmable Gain, Current-Sense Amplifier with Wide Measurement Range

 $(V_{CM} = V_{RS+} = V_{RS-} = +50V, V_{DD} = +3.3V, V_{SENSE} = V_{RS+} - V_{RS-} = 0V, V_{REF1} = V_{DD}/2, V_{REF2} = V_{DD}/2, G = 20V/V, T_A = -40^{\circ}C \text{ to } +125^{\circ}C, \text{ unless otherwise noted. Typical values are at } T_A = +25^{\circ}C \text{ (Note 1)}$

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS		
DC LOGIC CHARACTERISTICS (SDA, SCL, A0)								
Input Voltage High	V _{IH}		70			% of V _{DD}		
Input Voltage Low	V _{IL}				30	% of V _{DD}		
Output Voltage Low	V _{OL}				0.4	V		
Input Capacitance	C _{IN}			3		pF		

Note 1: All devices are 100% production tested at T_A = +25°C. Limits over the operating temperature range and relevant supply voltage range are guaranteed by design and characterization.

Note 2: Guaranteed by design and bench characterization.

Note 3: Gain is calculated based on two points measurements: V_{SENSE1} and V_{SENSE2}. V_{SENSE1} = -1V/Gain and V_{SENSE2} = 1V/Gain.

Typical Operating Characteristics



Bidirectional, On-The-Fly Programmable Gain, Current-Sense Amplifier with Wide Measurement Range



Bidirectional, On-The-Fly Programmable Gain, Current-Sense Amplifier with Wide Measurement Range



Bidirectional, On-The-Fly Programmable Gain, Current-Sense Amplifier with Wide Measurement Range

(V_{CM} = V_{RS+} = V_{RS-} = +50V, V_{DD} = +3.3V, V_{SENSE} = V_{RS+} - V_{RS-} = 0V, V_{REF1} = V_{DD}/2, V_{REF2} = V_{DD}/2, G = 20V/V, T_A = +25°C, unless otherwise noted.)



Bidirectional, On-The-Fly Programmable Gain, Current-Sense Amplifier with Wide Measurement Range



Bidirectional, On-The-Fly Programmable Gain, Current-Sense Amplifier with Wide Measurement Range

 $(V_{CM} = V_{RS+} = V_{RS-} = +50V, V_{DD} = +3.3V, V_{SENSE} = V_{RS+} - V_{RS-} = 0V, V_{REF1} = V_{DD}/2, V_{REF2} = V_{DD}/2, G = 20V/V, T_A = +25°C, unless otherwise noted.)$



Analog Devices | 11

Bidirectional, On-The-Fly Programmable Gain, Current-Sense Amplifier with Wide Measurement Range

 $(V_{CM} = V_{RS+} = V_{RS-} = +50V, V_{DD} = +3.3V, V_{SENSE} = V_{RS+} - V_{RS-} = 0V, V_{REF1} = V_{DD}/2, V_{REF2} = V_{DD}/2, G = 20V/V, T_A = +25^{\circ}C, unless otherwise noted.)$



CAPACITIVE LOAD (nF)



Bidirectional, On-The-Fly Programmable Gain, Current-Sense Amplifier with Wide Measurement Range



Pin Configurations



Pin Descriptions

PIN	NAME	FUNCTION
1	RS+	Positive Current-Sensing Input. Power side connects to external sense resistor.
2	RS-	Negative Current-Sensing Input. Load side connects to external sense resistor.
3	GND	Ground. Should be connected to a solid ground plane for best performance.
4	OUT	Current-Sense Voltage Output. V _{OUT} is proportional to V _{SENSE} .
5	VDD	Supply Voltage Input. Bypass V_{DD} to GND with a 0.1µF capacitor.
6	REF2	Reference 2 Input. REF2 and REF1 determine whether the device is used as uni or bidirectional.
7	REF1	Reference 1 Input. REF2 and REF1 determine whether the device is used as uni or bidirectional.
8	A0	I ² C Address as explained in the <u>Detailed Description</u> section.
9	SCL	I ² C Clock.
10	SDA	I ² C Data.
-	EP	Exposed Pad. Internally connected to GND.

Detailed Description

The MAX49918 is a high-precision current-sense amplifier (CSA) with an I²C programmable gain option from 10V/V to 200V/V in 8 steps. The multiple programmable gain options offer maximum flexibility for the user to change gain on-the-fly.

The MAX49918 operating input common-mode ranges from -5V to +70V, with protections that extend down to -6V and up to +80V, thus providing protection against reverse-battery and high-voltage spikes.

The low input offset of $\pm 1\mu V(typ)$ and low gain error of $\pm 0.01\%(typ)$ make the device well-suited for high-precision current measurements.

The MAX49918 operates from a supply voltage of +2.7V to +5.5V, with a typical quiescent supply at 0.7mA.

Programmable Gain

The MAX49918 features a programmable gain through I^2C . There are eight gain options with the following values in V/V: 10, 20, 40, 50, 80, 100, 160, and 200.

I²C Device Address

The MAX49918 uses an input pin (A0) that determines the least-significative bit (LSB) of the I²C device address word below.

BIT 6	BIT 5	BIT 4	BIT 3	BIT 2	BIT 1	BIT 0
1	1	0	0	1	0	A0

I²C Gain register

The register address to set the gain is 0x00. And the data to set the gain is in the table below.

GAIN	10	20	40	50	80	100	160	200
DATA (Hex)	0	1	2	3	4	5	6	7

Application Information

Output Voltage

The MAX49918 has two reference inputs (REF1 and REF2) to set the device in either unidirectional or bidirectional operation mode. Connect the REF1 and REF2 inputs to low-impedance voltage source(s) to set the MAX49918 output (V_{OUT}) reference level. Do not connect REF1 and REF2 inputs to any voltages lower than GND or higher than VDD. VRFF is defined as the average voltage of VRFF1 and VRFF2, i.e., the output voltage refers to VRFF = (VRFF1 + VRFF2)/2.

Use the following equation to set the gain:

V_{OUT} = V_{SENSE} x GAIN + V_{REF}

Where $V_{SENSE} = V_{RS+} - V_{RS-}$, and GAIN is the voltage gain of the MAX49918.

Ground-Referenced Output

Connect REF1 and REF2 inputs together and to ground. In this mode, the output is referenced to ground, and the output is taken to ground when the voltage drop across R_{SENSE} is 0V. The output voltage then increases proportionally to the voltage drop (V_{SENSE}) from RS+ to RS-.

V_{DD}-Referenced Output

Connect REF1 and REF2 inputs together and to V_{DD} . In this mode, the output is referenced to V_{DD} , or the output is taken to V_{DD} when the V_{SENSE} is 0V. The input V_{SENSE} must be negative to decrease the output voltage.

Setting Output to Mid-Supply Voltage

Connect REF1 to V_{DD} and REF2 to ground. In this mode, it creates a ratio-metric offset to the supply voltage, which means if V_{DD} increases or decreases, the output remains at V_{DD}/2 when there is no V_{SENSE}. This configuration is useful when external references are not available for offsetting the output.

Setting Output to Mid-External Reference

Connect one reference input pin to a reference voltage source and the other to ground. In this case, V_{OUT} refers to the external reference voltage divided by 2.

Setting Output to External Reference

Connect both reference input pins together to a reference voltage, which creates an output voltage equal to the reference voltage when the voltage drop across R_{SENSE} is zero. The output decreases when the input V_{SENSE} is negative. The output increases when the input V_{SENSE} is positive.

Ordering Information

PART NUMBER	DIE TYPE	PACKAGE	PACKAGE CODE
MAX49918IATB+T	OW05A-0A	TDFN-CU	T1033+1C

T = Tape-and-reel.

Revision History

REVISION	REVISION	DESCRIPTION	PAGES
NUMBER	DATE		CHANGED
0	9/23	Initial release	—



Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.